CI/SFB			
	×1.7		
	Xt6		



MASONRY CRACK STITCHING SYSTEM

CRACK STITCHING

DESCRIPTION

- High tensile helical reinforcing bars.
- Tensile strength twice that of rebar.
- Corrosion resistant stainless steel 304 and 316 grade.
- Use with WHO-60 high performance grout.
- Independently performance tested.

APPLICATIONS

- Reconnecting and strengthening cracked brickwork.
- Reinforcing masonry corners.

BENEFITS

- Deep interlocking helix offers excellent bonding characteristics.
- Increases tensile and shear strength of masonry.
- Accommodates thermal and moisture movement.
- Absorbs stress to redistribute load.
- Minimal disturbance and fully concealed repair.
- Quick, reliable and cost effective.

PRODUCT SPECIFICATION

Thor Helical crack stitching bars are available in 5, 6, 7, 8 and 9mm diameter, in standard lengths of: 1m and 2m

www.thorhelical.com • enquiries@thorhelical.com

STEPS







Clear debris from the slot and thoroughly flush out with water.





Pump a bead of WHO60 grout to the back of the slot to approximately 10mm from the surface.



 Push Thor bar half way into the grout-filled slot, trowel back displaced grout and re-point.



t: 0845 123 4004



MASONRY CRACK STITCHING SYSTEM

EN845-1 2013 +A1:2016 THB-15/220129

BS EN 845-1:2013 National Annex NA states that the bars need to provide an equivalent performance to the prescriptive 30mm x 5mm lateral restraint straps and the tension straps should have a declared mean tensile load capacity of at least 8kN.

TYPICAL TENSILE PERFORMANCE – CE MARK TESTING TO BS EN 845-1

Bar Diameter	No. of Bars per Joint	Mean UTL (kN)	Mean Load at 2mm Deflection		
6mm	1	8.39kN	6.26kN		
7mm	1	9.57kN	6.41kN		
8mm	1	11.06kN	8.73kN		
9mm	1	11.50kN	8.40kN		
6mm	2	16.00kN	10.86kN		
7mm	2	17.65kN	11.99kN		
8mm	2	17.65kN	10.67kN		
5mm	3	14.34kN	6.89kN		

Depth of test slot: 30mm for single bar - 40mm for multiple bars

Height of test slot: 3mm greater than diameter of crack stitching bars

Position of test bars: 400mm embedment with multiple bars spaced 10mm apart.

TYPICAL PROPERTIES OF THOR HELICAL BARS					
Diameter	CSA (mm2)	0.2% Proof Stress	Ult Tensile Strength*	Mean Tensile Capacity #	
5mm	6mm ²	>880N/mm ²	1025-1225N/mm ²	7kN	
6mm	8mm ²	>870N/mm ²	1025-1225N/mm ²	9kN	
7mm	10mm ²	>880N/mm ²	1025-1225N/mm ²	11kN	
8mm	13mm ²	>790N/mm ²	1025-1225N/mm ²	14kN	
9mm	16mm ²	>850N/mm ²	1025-1225N/mm ²	17kN	

* Ultimate Tensile Strength is measured within a calibrated tolerance of +/- 2% # Mean Tensile Capacity is an indicative value derived from CSA x Mean UTS

TYPICAL PROPERTIES OF WHO-60 Grout			
Physical Properties	Strength		
Compressive Strength – 7 days	35N/mm ²		
Compressive – 28 days	55N/mm ²		
Tensile Strength – 28 days	5N/mm ²		
Flexural Strength – 28 days	12N/mm ²		
Young's modulus (fully cured)	13kN/mm ²		



www.thorhelical.com • enquiries@thorhelical.com

t: 0845 123 4004